F. EYE WASH & SAFETY SHOWER



2 HAND OPERATED SAFETY SHOWER

- ▶ **Shower -** Extra large drench shower head made of highly
- Pipe ISI marked GI pipe with powder coating for anticorrosion
- ▶ Valve SS stay open ball valve with yellow ABS push plate
- ▶ **Bowl -** Receptor bowl made of ABS and highly resistant to acid, alkali and oil among others
- ► Activation For shower Pull rod & For eyewash Push plate
- ▶ Water inlet and drain 1 1/4 inches BSP
- **Standard -** IS:10592:1982



22 PADDLE OPERATED SAFETY SHOWER

- Pipe ISI marked GI pipe with powder coating for anticorrosion
- ▶ Valve SS stay open ball valve with yellow ABS push plate
- ▶ **Bowl -** Receptor bowl made of ABS and highly resistant to acid, alkali and oil among others
- ► Activation Push plate and foot paddle
- ► Water inlet and drain 1/2 inches BSP inlet and 1¼ inches BSP drain
- **Standard -** IS:10592:1982



23 WALL MOUNTED EYE/FACE WASH

- ▶ Valve SS stay open ball valve with yellow ABS push plate
- Bowl Receptor bowl made of ABS and highly resistant to acid, alkali and oil among others
- ► Activation Push plate
- ▶ Water inlet and drain 1/2 inches BSP inlet and 1¼ inches BSP drain
- **Standard -** IS:10592:1982



24 EYE WASH BOTTLES

- ▶ Emergency Eye Wash Bottle, quantity 500 ml
- Portable, lightweight and wall mountable
- ► The eye wash bottles are designed to be filled with clear water
- Soft and effective eye wash can be delivered in seconds even if the person is lying down